

Shelter for four waste bins 240 I – flat roof TYPE: F5L 8470 00P4



Illustrational photograph

TECHNICAL DATA

Material Sheet thickness (profiles / lid / panels) Capacity for waste bins No. of modules Weight

Dimensions (W x D x H)

galvanized steel sheet 1,25 / 0,5 / 0,5 mm 4x 240 l waste bin 4 pcs

4 pcs 109 kg

2780 x 830 x 1265 mm

ATTRIBUTES

- Modern and aesthetic shelter with a durable and solid structure made of galvanized steel sheet.
- The shelter structure is resistant to sudden changes in weather conditions.
- Connecting elements, hinges and locks are protected against corrosion.
- The structure is equipped with a front door for inserting / removing the waste bin.
- Equipped with a cushioning pad for the lid and cylindric lock for the lid and door.
- Lid with fixing in the open position with the possibility of locking the bin lid with a chain for easy opening.
- Universal installation of the door and lid variable door opening (right / left) / lid (front / back).
- There are openings in the bottom profiles for anchoring to the surface (anchoring material is not included).
- The panel design of the shelter allows air circulation and thus reduces odours.
- Surface finishing is carried out with powder paint.
- Standardly delivered in anthracite colour.

COLOUR VARIATIONS

Anthracite (RAL 7016).

PRODUCT PURPOUSE

Product is designed as a shelter for placing of waste bin.

ADDITIONS

Other colours on request.

Versions for 120 l or 240 l waste bin are available. Delivered without anchoring material and waste bins.







TECHNICAL DATA SHEET



RECOMMENDATIONS BEFORE INSTALLATION

Before assembling and installing the product, carefully read the assembly instructions to familiarize yourself with the product.

It is recommended to prepare a suitable base on which the shelter will be installed before installing it. It is necessary to prepare a concrete base or a base with paving stones, however, the base must be flat. It is also recommended that the base is at least 10 cm larger than the area of the shelter structure. After assembling the structure, anchor it to the base with purchased 8-10 cm anchors (not included). One module is equipped with 4 pre-prepared anchor openings + 2 additional openings in the frame if necessary.